

22.281-XM-@



(TEST LEAD, STRAIGHT TO RIGHT-ANGLE 4MM BANANA PLUGS, SHROUDED, 32A)



- The 22.281 test lead is a CE Certified Test Lead with straight shrouded 4mm banana plug on one end and a right-angle shrouded banana plug on the other.
- Uses 14 AWG PVC wire.
- Length is designated in meters by the “X” in the part number.
Available lengths are: 0.25m and 1m
- Ratings:
 - Operating Voltage: 1000V (CATIII)
 - Current: 32 Amps
 - Contact Resistance: $\leq 0.0005\Omega$
 - Insulation Resistance: $\geq 500M\Omega$
- Materials:
 - Banana Body: Nickel Plated Brass
 - Cage Spring: Nickel Plated Beryllium Copper
- Color: The “@” in the model number represents color. Available colors:
-0 Black, -2 Red
- RoHS 3 Compliant, CE Certified