

PRODUCT-DETAILS

TY538M

CBL TIE 50LB 8IN NAT NYL PUSH MNT



General Information

Extended Product Type	TY538M
Product ID	7TAG009530R0007
EAN	5414363066279
Catalog Description	CBL TIE 50LB 8IN NAT NYL PUSH MNT
Long Description	Push Mount Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 185mm (7.3 Inches), Width of 4.8mm (0.19 Inches), Thickness of 1mm (0.04 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

Ordering

E-Number (Finland)	1381526
EAN	5414363066279
UPC	786210825519

Dimensions

Product Net Width	0.184 in 4.67 mm
Product Net Depth / Length	7.88 in 200.2 mm

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	500 piece
Package Level 2 Width	8 in 203 mm
Package Level 2 Height	6.6 in 168 mm
Package Level 2 Depth / Length	10.7 in 272 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19750325
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000577
Instructions and Manuals	TY538M

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5035 >> Push Mount Cable Ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

