

13A Socket Outlets



Description

Metalclad offers a tough and impact resistant range of accessories with a durable finish and protective coating.

Each product is supplied with a surface mount metalclad back box and in its own polybag, protecting it up to the point of installation.

Features

- Durable and tough finish with protective coating
- Supplied complete with surface mounting box with knockouts
- On marked switch indicator
- Captive and backed out terminals
- Terminals have clearly embossed markings
- Only one size 4mm screwdriver needed
- Terminals have large lead-ins
- Recessed earth bar
- Most products have angled terminals to aid installation
- 2 earth terminals on 2 gang sockets
- 25-year guarantee

Technical Specification

Voltage rating	250Vac
Current rating	13A per outlet
Contact gap	3mm

No user serviceable parts

Standards

- BS 1363 Part 2

Range

13Amp

1 gang DP switched	VM1207DP
2 gang DP switched	VM1209DP
1 gang SP switched	VM1207SP
2 gang SP switched	VM1209SP
1 gang unswitched	VM1206
2 gang unswitched	VM1208

Back Boxes - Knockouts

All knockouts are 20mm diameter

	Sides	Back
1g	5	1
2g	8	1

Terminal Capacity

	2.5mm ²	4mm ²	6mm ²	10mm ²
L & N	4	3	2	1