SIEMENS

Data sheet

6ES7972-0BA52-0XA0

product type designation

product description



PROFIBUS connector

PROFIBUS bus connector, RS 485, Fast Connect, without programming port, 90° SIMATIC DP, Connection plug for PROFIBUS up to 12 Mbit/s 90° cable outlet, Insulation displacement method FastConnect, without PG socket 15.8x 59x 35.6 mm (BxHxD)

suitability for use	For connecting PROFIBUS stations to the PROFIBUS bus cable
transfer rate	
transfer rate / with PROFIBUS DP	9.6 kbit/s 12 Mbit/s
interfaces	
number of electrical connections	
for PROFIBUS cables	2
 for network components or terminal equipment 	1
type of electrical connection	
• for PROFIBUS cables	Integrated insulation displacement terminals for 2-core PB FC installation cables
 for network components or terminal equipment 	9-pin sub D connector
type of electrical connection / FastConnect	Yes
mechanical data	
design of terminating resistor	Resistor combination integrated and connectable via slide switch
material / of the enclosure	plastic
locking mechanism design	Screwed joint
design, dimensions and weights	
type of cable outlet	90 degree cable outlet
width	15.8 mm
height	59 mm
depth	35.6 mm
net weight	36 g
ambient conditions	
ambient temperature	
 during operation 	-25 +60 °C
 during storage 	-40 +70 °C
during transport	-40 +70 °C
protection class IP	IP20
product features, product functions, product components / ge	eneral eneral
product feature	
• silicon-free	Yes
product component	
 PG connection socket 	No
strain relief	Yes
standards, specifications, approvals	
certificate of suitability	
 RoHS conformity 	Yes
 UL approval 	Yes

• to website. Selection guide for capies and connectors	8/16/2023 ©
 to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
internet link	
further information / internet links	
 according to IEC 81346-2 	XG
reference code	