

FEATURES

- Material: Mild steel
- IP66 rating
- Fully wall mountable
- Lockable

RS PRO Wall Boxes- Steel Wall Box

RS Stock No.: 842-8453



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description**RS Pro IP66 Mild Steel Wall Box**

From RS Pro, A range of mild steel wall mounted enclosures. Wall boxes are an excellent addition to any industry which has a clear need to store or secure items or electronics. You can find them on the walls of various workplaces and areas of interest. These wall boxes are rated at IP66 offering a great solution for protection. Although not fully waterproof, the durable and robust build ensures its contents are fully protected within both indoor and outdoor environments. All models are highly reliable and excellent quality.

General Specifications

Body Material	Steel
Number Of Doors	1
Colour	Grey
RAL Code	RAL 7032
Gland Plate	Yes
Sealing Gasket	No
Door Lock Type	Double Lock System
Chassis Plate	Zinc-coated steel 2.0mm
Transparent Door	No
Fixing Kit	Yes
Application	Electrical
External Mounting Type	Bracket
Internal Mounting Type	Panel
Special Features	IK10 Against Mechanical Impacts
For Protection Of	Sensitive Electrical Equipment

Mechanical Specifications

External Height	600 mm
External Depth	300mm
External Width	800 mm
Dimensions	600 x800 x300mm
Thickness	1.2 mm for enclosure & door

Protection Category

IP Rating	IP66
-----------	------

Approvals

Declarations	RoHS Certificate of Compliance
--------------	--------------------------------

Similar Products

Stock No.	Brand	Product Name	Colour	Body Material	Dimensions
775-5300	RS PRO	Steel Wall Box	Grey	Steel	300 mm x 250 mm x 150 mm
775-5788	RS PRO	Steel Wall Box	Grey	Steel	300 mm x 200 mm x 150 mm

Additional Information / Installation Diagrams / Illustrations / Accessories

Drawings:

