

## FEATURES

- Product finish classification
- Black enamelled inside and outside
- Pre-galvanised sheet steel
- Hot dipped galvanised inside and outside

## RS PRO Galvanised Steel Rigid Conduit Metal 25mm x 3.75m M25

RS Stock No.: 228-801



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

Black enamelled or galvanised heavy gauge welded steel conduit. Threaded at both ends and supplied with one coupling per 3.75 m length with the choice of 20 mm or 25 mm sizes. A wide selection of fittings and accessories are available to assist in the most demanding or effortless installations.

For Conduit Cables see stock no. [381-012](#) typically  
For Cable and Wire pulling lubricants see stock no. [196-3407](#) typically

### General Specifications

<b>Conduit Type</b>	Rigid
<b>Material</b>	Galvanised Steel
<b>Colour</b>	Metal
<b>Coating Material</b>	Uncoated

### Mechanical Specifications

<b>Nominal Diameter</b>	25mm
<b>Length</b>	3.75mm
<b>Thread Size</b>	M25

### Approvals

<b>Standards Met</b>	BS4568
----------------------	--------