



Datasheet

ENGLISH

RS PRO SP13 Cable Mount Connector

Stock No:

207-0625,207-0627,207-0629,207-0631,207-0632,207-0633



Technical Specifications:

Number of contact	2	3	4	5	6	7	9
Male contact face view	(2 1)	(1) (1) (1) (1) (1) (1) (1) (1) (1) (1)	(3° 4)	10 05 9 3 0 2 0 4	2 • 1 3 • • 6 4 • 5	210 7 065 30 04	2 • 9 • 7 3 • • 6 4 • • 5
Rated current (A)	13A	13A	5A	5 A	5 A	5A	ЗА
Contact diameter	Ø _{1.6×2}	Ø _{1.6×3}	Ø _{1×4}	Ø _{1×5}	Ø 1×6	Ø _{1×7}	Ø _{0.7×9}
Rated voltage(AC.V)	250V	250V	200V	180V	125V	125V	125V
Test voltage(AC.V)1 min	1500V	1500V	1500V	1000 V	1000V	1000V	1000V
Contact resistance mΩ	2	2	5	5	5	5	10
Wire size mm² /AWG	≤2/14	≤2/14	≤0.785/18	≤0.785/18	≤0.785/18	≤0.785/18	≤0.785/18

Product Details

The RS PRO SP13 series is a range of small but robust waterproof connectors, which are sealed to IP68. Threaded coupling ensures a secure connection, even in extremely harsh environments. Versions are available for in-line cable to cable and for cable to panel connections. Plugs and receptacles are available with either male pins or female sockets. These products are especially suited for use in indoor or outdoor applications where space is at a premium.


Features and Benefits


- Threaded Coupling
- IP68
- 2-9 Poles
- Cable to Cable and Cable to Panel Connections





Dimensional line drawings





Quality Standards







