

### Main

Range of product	TeSys T
Device short name	LT6CT
Product or component type	Current transformer

### Complementary

Current transformer ratio	400/1
Accuracy class	Class 5P
Precision limit factor	15
[Ui] rated insulation voltage	690 V
Diameter	10 mm
Cable cross section	300 mm <sup>2</sup>
Height	107 mm
Width	95 mm
Depth	25 mm
Product weight	0.55 kg

### Environment

Standards	BS 7626 IEC 60185
Ambient air temperature for operation	<= 50 °C

### Contractual warranty

Period	18 months
--------	-----------