



-1. Lindström Precision Tools

-1.1. ELECTRONICS AND FINE MECHANICAL PLIERS

- Precision snipe nose pliers developed according to the scientific ERGO™ process
- Material: High performance alloy steel
- Polished
- Numerically controlled machine grinding guarantees accuracy and contact, increasing the tools reliability and consistency
- Tough hardened 42-46 HRC
- Screw joint that minimizes friction and maximizes jaw alignment
- ESD safe handles in 2-component synthetic material
- Micro-Touch: The shape of the handles makes it possible to control and rotate the pliers between thumb and index finger for precision work
- Biospring that limits the tension throughout the working cycle of the tool and can be adjusted in three different positions or removed
- 32 mm jaws with radiused edges
- RX 7890 with smooth jaws
- RX 7891 with serrated jaws

Rx Series Snipe nose pliers

RX 7890, RX 7891



| | | | | A mm | B mm | C mm | D mm | E mm | F mm | |
|----------------|--|---------------|----|---------|---------|---------|---------|---------|---------|----|
| RX 7890 | | 7314150103218 | 10 | 158.5 | 32 | 9 | 6 | 1.2 | 0.8 | 72 |
| RX 7891 | | 7314150103225 | 10 | 158.5 | 32 | 9 | 6 | 1.2 | 0.8 | 72 |

