


Black Elastic Rubber Trolley Wheel 300mm Hub 25, 700kg

Black Elastic Rubber-tyred wheel

PRODUCT

Article number

55-517-300B25



Product Details

Wheel Rim : lightweight aluminium alloy, reinforced safety design

Tyre : solid, black elastic rubber, bonded to the rim.

Hub : symmetrical, with two precision ball bearings.

Specifications

Wheel Diameter - ØD ± 1%	300 mm
Hub Type	two ball bearings
Hub Length T1	60 mm ±1
Width of Tread T2	57 mm ±1
Width of Tread-on floor T3	55 mm ±1
Axle Hole Ø d	Ø 25 mm
Hardness of tread A ±4	A 75 Shore
Load capacity	700 Kg
Temperature	-20 / +60 °C
Weight	2,68 Kg

TECHNICAL DATA

Applications :

Flexible materials handling for heavy loads on uneven surfaces.

Resilient with a low starting effort.

Lightweight wheel, resistant to wear and to side impacts.

Quiet in use. Reduce shock and vibration.

Suitable for trolleys on outdoor or industrial floors (factory, warehouse, truck transport,...).

Towable by mechanized vehicle (max.speed 4Km/h)