



mecalectro

Small linear solenoid for standard use – 8.M11.AA.62 (Push)



Stroke: 6 mm

Force at beginning of stroke (FM: 100/25/5%):
0.3/1.7/5.6 N

Force at end of stroke (FM: 100/25/5%):
4.3/10/15 N

Power Consumption (FM: 100/25/5%):
4/13.5/60 W

Total mass: 55 g

Degree of protection / Energetic class: IP 00 / B
Standard supplies: 24Vcc

Possible supplies: From 6 to 48Vcc

Duty Cycle: Permanent, impulses (100 / 40 / 25 / 15 / 5 %)

Standard: NF C 79300

Examples of applications: Automatism and small mechanism