

7511 // MOTION TEX LIGHT

Trousers



Breathable and light-weight material

Elastic waist

Practical and functional details



7511 // MOTION TEX LIGHT



Shell fabric:	Polyester / cotton, royal blue / navy blue
Lining:	-
Size(s):	24-29, 42-68, 90-110
Packaging unit:	10 piece(s)
Certification:	OEKO-TEX STANDARD 100®

NITRAS MOTION TEX LIGHT, long work trousers, royal blue / navy blue (colour code: 2021), 245 g/sqm, breathable and light-weight material, high wearing comfort, elastic waist, reinforcements on back belt loop, knee, back and leg pockets, reflective elements for better visibility, practical and functional details: thigh pocket with flap, ruler pocket with additional pocket, knee pockets for protectors with insertion from below, hammer loop, OEKO-TEX STANDARD 100®, Regular Fit



Industries



Automotive manufacturing



Commissioning / shipping

Advantages

- + Breathable and light-weight material
- + Elastic waist
- + Practical and functional details



Further images



Colour variants



7511 // MOTION TEX LIGHT
Colour code: 2021



7510 // MOTION TEX LIGHT
Colour code: 1000



7512 // MOTION TEX LIGHT
Colour code: 1210



7513 // MOTION TEX LIGHT
Colour code: 1112



7514 // MOTION TEX LIGHT
Colour code: 3010

Additional information

	Material	Colour	Grammage
Shell fabric	65% Polyester 35% Cotton	royal blue / black	245 g/qm



Machine wash 60°C



Do not bleach


Tumble dry, low
temperature


Warm iron



Dry cleaning possible

Wash separately or with similar colours. Close all zippers before washing and wash inside out. Applies only to non refined products. Do not use fabric softener. Think sustainably and wash at 30° C.

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
24	4059904067929	4059904067936	0,39 m	0,31 m	0,23 m	6,53 kg	40
25	4059904067943	4059904067950	0,4 m	0,34 m	0,24 m	7,07 kg	40
26	4059904067967	4059904067974	0,39 m	0,33 m	0,25 m	7,67 kg	40
27	4059904067981	4059904067998	0,4 m	0,33 m	0,24 m	7,11 kg	40
28	4059904068001	4059904068018	0,41 m	0,33 m	0,25 m	7,46 kg	40
29	4059904068025	4059904068032	0,39 m	0,32 m	0,24 m	7,52 kg	40
42	4059904068049	4059904068056	0,4 m	0,32 m	0,23 m	6,14 kg	40
44	4059904068063	4059904068070	0,41 m	0,32 m	0,24 m	6,56 kg	40
46	4059904068087	4059904068094	0,4 m	0,33 m	0,24 m	6,82 kg	40
48	4059904068100	4059904068117	0,4 m	0,32 m	0,25 m	7,02 kg	40
50	4059904068124	4059904068131	0,41 m	0,31 m	0,27 m	7,2 kg	40
52	4059904068148	4059904068155	0,37 m	0,35 m	0,24 m	7,57 kg	40
54	4059904068162	4059904068179	0,37 m	0,35 m	0,24 m	7,57 kg	40
56	4059904068186	4059904068193	0,41 m	0,33 m	0,24 m	7,71 kg	40
58	4059904068209	4059904068216	0,4 m	0,33 m	0,24 m	7,92 kg	40
60	4059904068223	4059904068230	0,4 m	0,32 m	0,24 m	8,04 kg	40
62	4059904068247	4059904068254	0,4 m	0,33 m	0,24 m	8,22 kg	40
64	4059904068261	4059904068278	0,41 m	0,33 m	0,24 m	8,18 kg	40
66	4059904068285	4059904068292	0,41 m	0,33 m	0,23 m	8,11 kg	40
68	4059904068308	4059904068315	0,4 m	0,34 m	0,24 m	8,48 kg	40
90	4059904068360	4059904068377	0,42 m	0,34 m	0,25 m	6,54 kg	40
94	4059904068384	4059904068391	0,4 m	0,31 m	0,23 m	6,8 kg	40
98	4059904068407	4059904068414	0,4 m	0,31 m	0,4 m	7,03 kg	40
102	4059904068421	4059904068438	0,4 m	0,32 m	0,24 m	7,91 kg	40
106	4059904068445	4059904068452	0,39 m	0,32 m	0,23 m	8,09 kg	40
110	4059904068469	4059904068476	0,41 m	0,33 m	0,23 m	8,09 kg	40

Customs tariff number: 62034311000

Country of origin: India