

M12 Cable Assembly D-cod st/st m/m 60m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 929 2477 600
Specification	M12 Cable Assembly D-cod st/st m/m 60m
HARTING eCatalogue	https://harting.com/21349292477600

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Straight
Connector 2	M12 D-coding Male Straight
Type of cable	Copper cable (round)

Version

Cable length	60 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-25 ... +70 °C

Material properties

Material (cable)	PUR (polyurethane)
------------------	--------------------



Pushing Performance
Since 1945

Material properties

Colour (cable) Green

Specifications and approvals

Specifications	UN/ECE-R 118 fire protection for rolling stock
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	3,845 g
Country of origin	Czechia
European customs tariff number	85444290
GTIN	5713140247697
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600
