

ToLEDo GLS

ToLEDo GLS 6.5W 470LM 827 B22 SL

0026390

Range features



CE

PRODUCT OVERVIEW

Light colour	827 Homelight
Technology	LED
Ordering number	0026390
Average life (Rated) (h)	15000
Energy class	A+
Lamp shape	GLS
Lamp finish	Frosted
Dimmable	No
Cap/Base	B22
Type	ToLEDo GLS
EAN code	5410288263908
CRI (Ra)	80
Colour temperature (K)	2700
Useful luminous flux (Rated) (lm)	470
Watt (Nominal) (W)	6.5
Equivalent watt (W)	40
Voltage (V)	220-240

ToLEDo GLS

ToLEDo GLS 6.5W 470LM 827 B22 SL

0026390

DATA TABLE

General data

Ordering number	0026390
Dry applications use only	Yes
Technology	LED
Average life (Rated) (h)	15000
Average life (Nominal) (h)	15000
Energy saving lamp	Yes
Energy class	A+
Lamp shape	GLS
Lamp finish	Frosted
Dimmable	No
Cap/Base	B22
Type	ToLEDo GLS
EAN code	5410288263908
Product name	ToLEDo GLS 6.5W 470LM 827 B22 SL
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Intended purpose	No
No. of switching cycles before premature failure (min)	20000
Special purpose lamp	No
Sales pack quantity	1
Optimal operating condition (°C)	25

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Useful luminous flux (Rated) (lm)	470
Lumen maintaining at end of nominal Life (lm)	70
Luminous flux (Nominal) (lm)	470

Electrical data

Watt (Rated) (W)	6.5
Equivalent watt (W)	40
Watt (Nominal) (W)	6.5
Voltage (V)	220-240
Lamp power factor	0.7

ToLEDo GLS

ToLEDo GLS 6.5W 470LM 827 B22 SL

0026390

Physical data

Lamp Length (mm) - C/L	108
Lamp Diameter (mm) - D	60

ToLEDo GLS

ToLEDo GLS 6.5W 470LM 827 B22 SL

0026390

TECHNICAL DRAWINGS

