



## Easy to use guide VLT® Micro Drive

Danfoss Drives, Ulsnaes 1, DK-6300 Graasten, Denmark, Tel. +45 74 88 22 22, Fax +45 74 65 25 80  
[www.danfoss.com/drives](http://www.danfoss.com/drives) • E-mail: [info@danfoss.com](mailto:info@danfoss.com)

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.  
 DKDD.PB.23.A1.02 VLT® is a trademark of Danfoss A/S Produced by KKM 2006.07

# Easy to use guide VLT® Micro Drive

# VLT® Micro Drive selection guide



## Cabinet sizes (mounting brackets incl.)

[mm]	M1	M2	M3*
Height	150	180	Available 2007
Width	70	75	
Depth*	148	168	

+ 6 mm with potentiometer

## Ordering numbers

Power [kW]	Current [I-nom.]	200 V		400 V	
		1 ph.	3 ph.	Current [I-nom.]	3 ph.
0.18	1.2	132F 0001			
0.25	1.5		132F 0008		
0.37	2.2	132F 0002	132F 0009	1.2	132F 0017
0.75	4.2	132F 0003	132F 0010	2.2	132F 0018
1.5	6.8	132F 0005	132F 0012	3.7	132F 0020
2.2	9.6	132F 0007	132F 0014	5.3	132F 0022
3.0				7.2	132F 0024
3.7	15.2		132F 0016		
4.0				9	132F 0026
5.5		Micro drives from 1.5 kW and up have built in brake chopper		12	132F 0028
7.5				15.5	132F 0030



VLT® Control panel LCP 11  
W/o potentiometer.....132B0100



VLT® Control panel LCP 12  
With potentiometer.....132B0101



Remote mounting kit  
incl. 3 m cable.....132B0102

NEMA 1 kit for M1  
Codeno.....132B0103

NEMA 1 kit for M2  
Codeno.....132B0104

NEMA 1 kit for M3  
Codeno.....132B0105

Decoupling plate  
For M1 and M2.....132B0106

Decoupling plate  
For M3.....132B0107