



6-641335-3 | MP-64U-F-1
Modular Plug, 6P/4C, Unshielded, Flat Oval, 100 pcs

Body Features

Conductor Type Solid | Stranded

Configuration Features

Number of Positions 6
Keyed No

Contact Features

Contact Base Material Phosphor bronze
Contact Mating Area Plating Material Gold
Contact Mating Area Plating Thickness 50.00 μin | 1.27 μm
Number of Contacts Loaded 4

Dimensions

Cable Jacket Outside Diameter Range 0.09–0.26 in | 2.29–6.61 mm
Conductor Outside Diameter 0.034–0.039 in | 0.86–0.99 mm
Conductor Wire Size 26–24 AWG

Housing Features

Housing Material Glass filled polycarbonate

Industry Standards

UL Flammability Rating UL 1863

Packaging Features

Packaging Quantity 100

Product Availability

Region Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Features

Cable Type Flat oval, unshielded
Performance Category Category 3
Connector Style Plug
Jack Type RJ11
Latch Style Standard

6-641335-3 | MP-64UF-1

Product Type	Connector
Shielded	No

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
----------------------------------	-------------------------------------