

Rotary Hammer LXT®

DHR243

18V • SDS-PLUS • 24 mm • 2.0 J

Brushless, three-mode rotary hammer with quick-change chuck

An efficient rotary hammer with an anti-vibration handle and quick-change chuck that accepts SDS-PLUS bits. Suitable for impact and unstressed drilling, plus chipping. Speed range of 0 – 950 min⁻¹. Impact energy of 2.0 J and max. drilling capacity of 24 mm in concrete.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Impact Energy	2,0 J
Optimum Drilling Diameter Range in Concrete	4 - 16 mm
Max. Drilling Diameter in Concrete	24 mm
Max. Drilling Diameter in Wood	27 mm
Max. Drilling Diameter in Steel	13 mm
Impacts per Minute (IPM)	0 - 4700 min ⁻¹
No load speed	0 - 950 min ⁻¹
Drilling diameter with TCT core bit	54 mm
Adapted for SDS-PLUS bits	✓
Tool weight with battery	3,2 - 3,7 kg
Electronic brake	✓

User benefits

- 3-Mode operation for "Rotation Only", "Hammering with Rotation" or "Hammering Only" for multiple applications
- Brushless maintenance-free and long-life motor
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Optional AC

194079-2

Quick Change Drill Chuck 13 mm,

324219-0

Depth Gauge

450128-8

Battery cover, LXT®, 14,4 – 18V

835A31-4

MakPac Type 4 Inlay

B-14059

Scaling Chisel, 40 x 250 mm

P-25105

Wood Chisel SDS-PLUS, 20 x 170

P-35184

SDS-Plus Shank 32 - 152mm



199557-7

Replacement Hepa filter



424474-5

Sealing Cap



821552-6

Makpac case (4)



837649-1

MakPac (4) Inlay



D-14093

Chuck Adapter SDS-Plus -



P-25111

Wood Chisel SDS-PLUS, 30 x 170



Other

User manual

Parts drawing