

Office Mouse, Hybrid

00182691 "EMW-700" Ergonomic Vertical Mouse, Rechargeable, Multi-Device, anthra.



Highlightstext:

- This first-class, high-tech mouse is the epitome of "multi": an all-rounder offering ergonomics at the workstation, when connecting devices and during connection – the vertical mouse with superlative performance for improved productivity at the workstation
- One vertical mouse for all: no tedious reconnecting - with just one click, easily switch between up to three devices - 2 x Bluetooth 4.2 and 1 x 2.4 GHz
- Bye bye mouse arm: the ergonomic mouse supports a natural angle between the hand and wrist at an ergonomic workstation, thereby preventing shoulder pain, tendon sheath inflammation and pain in the wrist
- Vertical mouse chargeable at the USB-C socket: tedious battery changing is a thing of the past, helping to promote sustainability. Particularly efficient: you can continue to use the ergonomic mouse while it's charging
- Light effect at the desk: vertical mouse with colourful RGB colour change - for that gaming feel in the office
- dpi switch for adjusting the pointer speed
- High-resolution optical sensor ensures precise and smooth control of the mouse cursor
- Browser buttons provide quick access to the forward/back function for easy navigation, e.g. in web browsers, Outlook, etc.
- Storable USB receiver can be transported inside the mouse to save space
- Separate on/off switch allows for energy-saving use of the mouse
- Built-in rechargeable Li-ion battery. When the battery is flat, simply charge it with the charging cable (runtime approx. 85 days with everyday use)
- The ideal ergonomic mouse for anyone who works with a tablet, PC etc. simultaneously
- Switchable sensitivity between 1000, 1600 and 2400 dpi
- 2.4 GHz radio technology and Bluetooth 4.2 for reliable, interference-free and fast signal transmission - a small LED light directly on the vertical mouse shows you which mode is currently set
- Radio range of up to 10 m (depending on the conditions of use and surroundings)
- The RGB illumination can be switched off

System Requirements:

- Windows 11/10/8, Android 4.3 or later, MacOS 10.10 or later, iOS 13 or later operating systems

Technical characteristics:

- Colour: Grey
- Form factor: Right handed
- Shade of colour: Anthracite
- Connection: 2.4 GHz RF/Bluetooth
- Connection: USB-Typ-A-Plug
- Battery life (depending on usage): 36 d
- Bluetooth Version: 4.2
- Compatible operating systems: Android 4.3 or higher/MAC OS 10.10 or higher/Windows 11/10/8/iOS 13 or higher
- DPI-Range: 1000/1600/2400
- Max. DPI: 2400
- Range: 10 m
- Special features: Browser key/Dual mode/Lighting/On/Off Switch/Variis dpi-Stages
- Model: Ergonomic/Standard Mouse
- Mouse - Keys: Standard
- Mouse - Sliding Pads: Polytetrafluoroethylene (PTFE)
- Mouse wheel (material): Metal
- Number of Mouse Buttons: 8 Buttons incl. Scroll Wheel
- Number of dpi buttons: 1

Office Mouse, Hybrid**00182691 "EMW-700" Ergonomic Vertical Mouse, Rechargeable, Multi-Device, anthra.**

- Sensors: Optical
- Cable length (charging cable): 0,80 m
- Weight (including battery): 125 g
- Width x Height x Depth: 8.5 x 7.5 x 11.5 cm
- Battery Type: Lithium-Ionen
- Charging Method: USB-C socket
- Number of Batteries: 1
- Power supply included: No
- Required high performance power supply: 2.0 W
- Required minimum power supply: 2.0 W
- USB PD: No

Delivery:

- 1 "EMW-700" ergonomic vertical mouse
- 1 USB-A receiver
- 1 USB-A - USB-C charging cable
- 1 operating manual

 4 047443 499073	Brand	Item-no.	VE	MB
	hama	00182691	8	1