

ANSMANN Press Release

AS 10 H+

„Industrial Work light with halogen and LED light source“

The industrial flashlight AS 10 H+ is a brand new development from the torch specialist ANSMANN. It is robust, bright and depending on the selected light source, up to 120 hours operating time. The main light source is a halogen bulb with a power of 6 W. With the focusable reflector, the light carries up to about 1200 metres. The operating duration with the halogen bulb is about 3 hours. The rubberized housing is very handy and can also be used with gloves and is dirt and splash-proof according to IP 44. A very smart function is the LED light strip on the bottom side of the light. This very soft and diversified light is excellent as a “light for the ground” when walking or for the illumination of maps on tables or on vertical surfaces.

At the same time, the LED is very efficient (lighting duration up to 120 hours). In case the battery capacity is too low, the light source switches automatically from halogen to LED operation – afterwards, there is still more than one hour light available.

The micro controlled fast charger just needs 3.5 hours for one complete charge! The power supply is suitable for worldwide use; the car charger is usable in cars and lorries which is perfect for emergency aid organisations and industry. ANSMANN offers the set completely with both chargers and one NiMH-battery pack with a guarantee of two years.



Contact:

ANSMANN AG
Industriestraße 10
D-97959 Assamstadt
Germany
Phone: +49 6294 / 4204-0
Fax: +49 6294 / 4204-44
E-Mail: info@ansmann.de
Web: www.ansmann.de