

Product data sheet

Specifications



APC Service Bypass Panel, 230V, 125A, 2x hardwire input connectors, 8x IEC 60320 C19 outlets

SBP20KRMI4U

Overview

Lead time Usually in Stock

General

Provided equipment Installation guide
Rack mounting brackets
User manual

Physical

Colour Black
Depth 57.2 cm
Height 17.8 cm
Net weight 18.78 kg
Width 43.2 cm

Input

Network frequency 50/60 Hz
Number of input connectors 1 hard wire 3-wire (1P + N + E)
1 hard wire 5 wire (3P + N + E)
Number of cables 1
Max line current 125 A
Input current limits 125 A
Load capacity 20000 VA
Power factor 0...1
Input voltage 220 V
230 V
240 V
380 V 3 phases
400 V 3 phases
415 V 3 phases

Output

Max current draw 125 A
Number of power socket outlets 8 IEC 60320 C19
Protection type Circuit breaker

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Efficiency	99 %
Output voltage	230 V

Conformance

Product certifications	CSA GOST
Standards	EN 60950 IEC 60950 IEC 60950 UL 1778

Environmental

Ambient air temperature for operation	-20...50 °C
Relative humidity	0...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-40...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	31.36 kg
Package 1 Height	30.5 cm
Package 1 width	61 cm
Package 1 Length	84.3 cm
Number of Units in Package 3	6

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years (parts only)
----------	----------------------
