



Datasheet

RS Pro, 750VA Isolation Transformer, 230V

RS Stock No: 123-7380



RS Pro 0.75 kVA continuously rated transformer, single phase, 230 V ac input -110 V ac output. These safety site transformers are high quality, UK manufactured to BSEN 61588 and fully compliant with reduced low voltage regulations. These Transformers are designed to ensure safe electrical distribution for power tools in industrial, garage and other fixed installations. Robust IP22 painted steel enclosure and complete with mounting flanges and conduit entry points. 110V ac output, 6 Amp thermal magnetic trip (hand resettable) reducing the chance of overload.

Standards: BS EN 61558, BS EN 61558-20-23, BS EN 60529 ,RoHS Directive 2011/65/EU

Attribute	Value
Primary Voltage Rating	230V
Secondary Voltage Rating	110V
Power Rating	750VA
Length	220mm
Width	152mm
Depth	223mm
Dimensions	220 x 152 x 223mm
Mounting Type	Wall Mount
Minimum Operating Frequency	50Hz