

WSP80 Robust

Item No: T0052917299N

Soldering iron robust 80 W, 24 V with Silver-Line Heating Technology



TECHNICAL DATA

Approximate Heating Time (50–350 °C/120–660 °F)	10 sec
Barrel	T0058744710
ESD Safe	Yes
Inert Gas Function	T0058744847
Integrated Direct Extraction	T0052918699 T0052918599
Power	80 W
Temperature Range (Depends on Tool)	50 - 450°C
Temperature Range °C	50 - 450 °C
Tip Type	LT
UPC	037103306838
Works With	PU 81 PUD 81 PUD 81i PU WAD 101 PUD 121 PU WAD 101IG PUD 151 WD 1 WD 1M WT 1 WT 1H WR 2 WR 3M WR 3ME
Weight (Catalog)	0.11 kg
Product Family	WT Soldering Irons