## ball valve VZBM-1/2-RP-50-D-2-M-B2B3 Part number: 4405686

Brass, manual version, 2/2-way, nominal width 1/2", PN50, thread EN 10226-1.

Festo is only a retailer of this product, not the manufacturer.



## **Data sheet**

Feature	Value
Design structure	2-way ball valve
Type of actuation	mechanical
Sealing principle	soft
Assembly position	Any
Mounting type	Line installation
Process valve connection	Rp1/2
Switching position indicator	Slot direction = flow direction
Inside diameter	15 mm
Nominal diameter DN	15
Valve function	2/2
Flow direction	reversible
Nominal pressure of process valve	50
Actuation moment at differential pressure, process valve nominal pressure	9 Nm
Based on the standard	EN 10226-1
Medium	Compressed air in accordance with ISO8573-1:2010 [-:-:-]
	Inert gases
	Water (no water vapour)
	Neutral fluids
Medium temperature	-15 120 °C
Flow rate Kv	15 m3/h
Materials note	Contains PWIS substances
	Conforms to RoHS
Material housing	Brass
	Nickel plated
Material number for housing	CW617N
Material seals	NBR
	PTFE
Material ball	Brass
	Chromed-plated
Material number for ball	CW617N
Material shaft	Brass
Material number for shaft	CW617N
Product weight	200 g
Authorisation	DVGW gas
	DVGW water
CE mark (see declaration of conformity)	to EU directive pressure devices
Corrosion resistance classification CRC	1 - Low corrosion stress

## **FESTO**