

# QOB130

## MINIATURE CIRCUIT BREAKER 120V 30A


[Download your QOB130 datasheet](#)


### Characteristics


#### Main

Hide

Product or component type	Miniature circuit-breaker
Range of product	QO
[In] rated current	30 A
Product certifications	CSA UL listed
[Ue] rated operational voltage	120/240 V AC
Mounting mode	Bolt-on
Poles description	1P
Short-circuit current	10 kA
Number of spaces required	1
Circuit breaker type	Standard
Circuit breaker application	HACR rated
Electrical connection	Pressure plate
AWG gauge	AWG 14...AWG 8 (copper or aluminium)
Accessory / separate part type	None

#### Offer Sustainability

Hide

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available  <a href="#">download Product environmental</a>
Product end of life instructions	Need no specific recycling operations

#### Contractual warranty

Hide

Period	18 months
--------	-----------