



Terminal, screw terminal, two-tier, equipotential bonding, through-type terminal, 2.5 mm², gray

Model	
product brand name	SETRON
product designation	Terminal blocks
design of the product	two-tier terminal
product variations	two-tier terminal internally bridged for mounting on mounting rail acc. to IEC 60715
design of terminal terminal levels internally linked	No
General technical data	
terminal contact spacing	5 mm
operating voltage rated value	500 V
Protection class	
combustibility class according to UL 94	V0
Main circuit	
operational current rated value	24 A
Appearance	
color	grey
Product details	
product component required end cover plate	Yes
Number	
number of terminal levels	2
number of terminal points per terminal level	2
Connections	
stripped length	9 mm
connectable conductor cross-section solid	
• minimum	0.14 mm²
• maximum	4 mm²
connectable conductor cross-section finely stranded	
• with core end processing minimum	0.1 mm²
• with core end processing maximum	3 mm²
tightening torque with screw-type terminals	
• minimum	0.6 N·m
• maximum	1 N·m
type of connection 1	screw-type terminal
type of connection 2	screw-type terminal
position of the terminal	lateral
Mechanical Design	
height with lowest-profile installation	65 mm
length	70 mm
fastening method	DIN rail 35 mm
net weight	17 g

material of the insulating body	Thermoplast	
Environmental conditions		
ambient temperature during operation		
• minimum	-60 °C	
• maximum	105 °C	
Approvals Certificates		
General Product Approval	Declaration of Con- formity	other



[Confirmation](#)



[Miscellaneous](#)

[Confirmation](#)

Environment

[Environmental Con-
firmations](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WH1025-0AF00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WH1025-0AF00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WH1025-0AF00

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

7/19/2023

