

Product Datasheet

HEAT-SHRINK BUTT CONNECTORS


Specifications and Dimensions:

SPECIFICATIONS						
MATERIAL:	COPPER					
MAX. VOLTAGE:	600 V					
MAX. CURRENT:	22-16 AWG: 19A 16-14 AWG: 27A 12-10 AWG: 48A					
SHRINK TEMP.:	150°C		WORK TEMP.:		-55°C ~ +125°C	
RS Article Code	D	d	B	L	COLOR	WIRE RANGE
8199870	5.8	1.7	15	36	RED	22-16AWG
						0.5-1.5mm ²
8199874	6.9	2.4	15	36	BLUE	16-14AWG
						1.5-2.5mm ²
8199883	8	3.6	15	42	YELLOW	12-10AWG
						4.0-6.0mm ²