2533 : Compact Manual Axial Crimping Tool for PEX series 5














The + product :

User-friendly: only one hand to crimp or declutch.
Gear units to crimp the coupling, elbow, T, nut and threaded.
The range is completed by Expansion Pliers Ø 12-20 mm.

Description

Specific crimping forks design to not damage the coupling during the crimping.
For crimping free nuts Ø 3/8, 1/2, 3/4" and Tees and elbows Ø 12, 16 and 20 mm. (Crimping fork in Ø 20 mm)
Suitable for installation or renovation in a house.
Ergonomic use with Soft Touch® handles.
Effortless handling for an easier work.
Die-cast aluminum design: strong and light weight (only 800g).

Expansion Pliers PEX series 5 : Sheathed handles for a better handling ; End caps treated with cataphoresis to reduce corrosion risk and to make easier the pipe fitting.

More Information

Capacity	PEX series 5 Ø 12 - 16 - 20 mm
Supplied with	2 gears Ø 12 mm (Réf. 753568), 2 gears Ø 16 mm (Réf. 753569), 1 double gear V (Réf. 753570), 1 flat double gear (Réf. 753571). In a case.

References

Sku	Description	kg
253360	Crimping tool box Ø 12 - 16 - 20 mm + expansion pliers Ø 12 - 16 - 20 mm	2,340
253350	Crimping tool box Ø 12 - 16 - 20 mm	2,000
253355	Expansion pliers Ø 12 - 16 - 20 mm	0,380
253361	Crimping tool box Ø 12 - 16 - 20 mm + expansion pliers Ø 12 - 16 - 20 mm + pipe cutter PC 32	2,540
753568	Gear Ø 12 mm	0,080
753569	Gear Ø 16 mm	0,080
753570	Gear V	0,080
753571	Flat double gear	0,080