


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS | | | |
|-----|------|-------------|---------------------------|---------|-------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| AF | 50 | N | REVISED PER ECR-13-004343 | 30JUL13 | KH KR |

- 1 MATES WITH .020±.001x.187 TAB
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .260 MAX DIA
- △4 DIMENSION DOES NOT INCLUDE TRIM BURR
- △5 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA



| | |
|--|-------------|
| HOUSING: NYLON, COLOR-BLUE TRANSLUCENT RECEPTACLE: BRASS TIN | 3-520151-2 |
| MATERIAL & FINISH | PART NUMBER |

| | | | | | |
|--|--|------------------------------|--|------------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN P FORTNEY 9/28/88 | TE Connectivity RECEPTACLE ASSY, ULTRA-FAST, LOOSE PIECE, .187 SERIES, 16-14 AWG | | |
| DIMENSIONS: INCHES | | CHK MS FEHER 9/28/88 | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD K RANDOLH 9/28/88 | | | |
| 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .015 4 PLC ± - ANGLES ± - | | NAME | | | |
| MATERIAL SEE TABLE | | FINISH SEE TABLE | PRODUCT SPEC 108-2043 | APPLICATION SPEC 114-2123 | RESTRICTED TO |
| CUSTOMER DRAWING | | | WEIGHT - | SIZE A3 | CAGE CODE 00779 |
| | | | DRAWING NO C-520151 | SCALE 4:1 | SHEET 1 OF 1 |
| | | | REV N | | |