

## 249G - SHEATHED DRIFT PUNCHES | 249.G2



### Description

- Long shank.
- Head hardened to 43 HRc.
- Shank hardened to 58 HRc.

### Information

A [mm] 1,95

d [mm] 8

L [mm] 140

L1 [mm] 35

L2 [mm] 105

[g] 88

[kg] 0,088

