Features

- Process Indicator
- Selectable Universal Process Input (0-10Vdc, 0-1Vdc, 0-60mV, 0-20mAdc, 4-20mAdc)
- 4 Digits Process (PV) display
- 24Vac/dc Power Supply
- Configurable display scale between -1999 and 9999
- Adjustable decimal point
- 1 SSR Driver Output (Max 28mA,15Vdc)

RS PRO Process Indicator

RS Stock No:
874147



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Process Indicator

Product Description

Selectable universal process Input
(0-10Vdc, 0-1Vdc, 0-60mVdc, 0-20mAdc, 4-20mAdc)
Configurable display scale between -1999 and 9999
4 Digits display
1 SSR Driver Output (Max. 28mA, 15Vdc)
Applications Fields:

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications

General Specifications

Supply Voltage and Power	24Vac/dc
Sensor Inputs	0-10Vdc, 0-1Vdc, 0-60mVdc, 0-20mAdc, 4-20mAdc)
Output	1X SSR Driver Output (Max. 28mA,15Vdc)
Accuracy	Scale ± %0.25

Mechanical Specifications

Dimension	77 mm x 35 mm 62,5 mm
Panel	IP65 at front, IP20 at rear
Max. Operating Temperature / Humidity	50°C / 90 % max. (None condensing)

Electrical Connection

