

Data of cable-assembly no.:

K-2165

Connector No.	4012.91.1420.021 4007.91.2120.021	Adapterkabel bzw. Verlaengerung fuer 3461								
Cabletyp made by:	RG 174 Nexans									
Mechanical-length	500	mm								
Impedance :	50	Ohm								
Specification of customer:	keine									
Return-loss S11 [dB] :	<table border="1"> <thead> <tr> <th>GHz</th> <th>dB</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>23</td> </tr> <tr> <td>2</td> <td>18</td> </tr> <tr> <td>2,5</td> <td>13</td> </tr> </tbody> </table>	GHz	dB	1	23	2	18	2,5	13	
GHz	dB									
1	23									
2	18									
2,5	13									
Insertion-loss S21 [dB] :	<table border="1"> <thead> <tr> <th>GHz</th> <th>dB</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>1</td> </tr> <tr> <td>2</td> <td>1,15</td> </tr> <tr> <td>2,5</td> <td>1,35</td> </tr> </tbody> </table>	GHz	dB	1	1	2	1,15	2,5	1,35	
GHz	dB									
1	1									
2	1,15									
2,5	1,35									
Proof Voltage (Veff/50Hz):	500	Veff								
Additional notes:	Last update:	16.01.2006								