

MULTIPORT WALL MANIFOLDS

Female thread wall bracket -
Couplers and drain - ISO 6150 C
profile



Part number	Female thread	Min. operating pressure (bar)	ID passage (mm)	Temperature min/max (°C)
MF 104S4CS	G3/4	0.00 / 16.00	6	-20.00 / 80.00
MF 104S6CS	G3/4	0.00 / 16.00	6	-20.00 / 80.00
MF 104S8CS	G3/4	0.00 / 16.00	6	-20.00 / 80.00

Part number	Dim. A (mm)	Dim. B (mm)	Dim. C (mm)	Dim. D (mm)	Dim. E (mm)
MF 104S4CS	78.00	135.00	63.00	80.00	6.50
MF 104S6CS	78.00	180.00	63.00	125.00	6.50
MF 104S8CS	78.00	225.00	63.00	170.00	6.50