



## Tavor 8-Sub

8-Inch Powered Subwoofer

| Speakers



The Tavor 8-Sub is a powered subwoofer that can be mounted on the wall, the floor or next to the wall in a way that hides the control panel. The product reproduces low-range audio frequencies and includes auto standby and adjustable crossover frequencies

### FEATURES

Type - Powered subwoofer

Woofers - 8" aluminum with rubber surround

Frequency Response - 30Hz to 600Hz @-10dB

Built In Power Amplifier - 50W RMS, 140W continuous program

Inputs - 1 line level stereo on RCA connectors, 1 LFE input on an RCA connector, 2 high-level inputs on binding posts for bypassing internal amplifier

Volume Level Knob

Crossover Frequency Adjustment - 65Hz to 150Hz on a control knob

Reverse Phase Selector - 0 or 180Deg

Optional Auto Standby

Selectable Power Settings - 110-120V AC, 220-240V AC



# KRAMER

## TECHNICAL SPECIFICATIONS

---

DESCRIPTION:	Subwoofer speaker
FREQUENCY RESPONSE:	30Hz to 600Hz @-10dB, 45Hz to 350Hz @±3dB
WOOFER:	8" (203mm) aluminum with rubber surround
IMPEDANCE:	200Ω (high level input)
SENSITIVITY:	95dB SPL, 1W @1m
MAX SPL:	Continuous: 108dB; peak: 114dB
POWER HANDLING:	50W RMS, 140W continuous program
POWER SOURCE:	Selectable: 110-120V AC 60Hz or 220-240V AC 50Hz
CROSSOVER FREQUENCY:	65-150Hz
INPUT CONNECTORS:	High-level unbalanced stereo audio on binding posts, LFE or Line level unbalanced stereo audio on RCA connectors
CONTROLS:	Volume, crossover, phase, auto standby and selectable power source
MATERIALS:	Wooden cabinet and wooden bracket
OPERATING TEMPERATURE:	-15° to +70°C (5° to 158°F)
STORAGE TEMPERATURE:	-30° to +55°C (-22° to 131°F)
HUMIDITY:	25% to 90%, RHL non-condensing
INCLUDED ACCESSORIES:	Power cable, 4 black rubber feet
COLOR:	White
Product Dimensions	45.00cm x 40.00cm x 20.50cm (17.72" x 15.75" x 8.07" ) W, D, H
Product Weight	10.3kg (22.6lbs) approx
Shipping Dimensions	0.00cm x 0.00cm x 0.00cm (0.00" x 0.00" x 0.00" ) W, D, H
Shipping Weight	13.2kg (29.1lbs) approx

