



Double-ended ratchet ring spanners, imperial, bi-hex

25a



Product no. **41561620**
GTIN **4018754164448**
Model **25a 1/4 x 5/16**



Label.

Double-ended ratchet ring spanner Size 1/4 x 5/16 " L.109mm

Properties.

- **imperial, differing** end sizes
- bi-hex with AS-Drive profile
- straight version
- 22 teeth
- made completely of steel, chrome-plated
- Fed. Spec. GGG-W-001405


Technologies and features.



Anti-Slip-Drive

The special AS-Drive profile makes high force transmission to the flats of screws and bolts possible without damaging them. This also prevents stripping of the screw head.

Technical drawing.



Technical attributes.

a	9 mm
Drive profile	bi-hex AS-Drive
d1	15 mm
d2	17 mm
Length mm (L)	109 mm
Alloy	All-steel
Size 1 [inch]	1/4 "
Size 2 [inch]	5/16 "

Logistics data.

Depth mm (IFS)	58
Width mm (IFS)	10
Height mm (IFS)	8
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	58
Width (packaged, mm)	10
Height (packaging, mm)	8
Volume (packaged, dm3)	0.00464 dm3
Product no.	41561620
Weight (gross, kg)	0,060
Weight PAP (kg)	0,000
Weight PVC (kg)	0,003
GTIN	4018754164448
Country of origin AWR	UNITED STATES
Region of origin	Ausländischer Ursprung
Customs tariff no.	82041100
Packing standard	1
Weight (g)	60 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
41561620	25a 1/4 x 5/16	Double-ended ratchet ring spanner Size 1/4 x 5/16 " L.109mm	4018754164448
41562022	25a 5/16 x 11/32	Double-ended ratchet ring spanner Size 5/16 x 11/32 " L.109mm	4018754164455
41562428	25a 3/8 x 7/16	Double-ended ratchet ring spanner Size 3/8 x 7/16 " L.139mm	4018754164462
41563234	25a 1/2 x 9/16	Double-ended ratchet ring spanner Size 1/2 x 9/16 " L.174mm	4018754164479
41563638	25a 5/8 x 11/16	Double-ended ratchet ring spanner Size 5/8 x 11/16 " L.205mm	4018754164486
41564044	25a 3/4 x 7/8	Double-ended ratchet ring spanner Size 3/4 x 7/8 " L.235mm	4018754164493
41564246	25a 13/16 x 15/16	Double-ended ratchet ring spanner Size 13/16 x 15/16 " L.235mm	4018754164509

GTIN.

