

Ferrite Channel Magnets



These are C -profile ferromagnetic mild steel channels within which are placed magnets. They have a rectangular shape and work in a similar way to pot magnets. The ferrite magnet versions can operate at temperatures up to a maximum of +120 degrees C.

The channel magnets have two 4.2mm diameter fixing holes in the mild steel back plate section to allow them to be screwed onto an assembly.



- 120 maximum operating temperature
- Excellent resistance to corrosion
- Mild steel pot with red painted body
- C profile channel

RS PART NO	ECLIPSE PART NO	PULL FORCE (kg)	Length (mm)	Height (mm)	Width (mm)	Weight (kg)	Plain Fix Holes (mm)	Hole Centres (mm)	DESCRIPTION
9175702	E899	48	190	13	43	0.55	4.2	110	190mm Ferrite Channel Magnet

All sizes and colours available from stock. Please get in touch for further information.

Eclipse Magnetics, Atlas Way, Sheffield, S4 7QQ, England
T +44(0)114 225 0613 info@eclipsemagnetics.com
F +44(0)114 225 0610 www.eclipsemagnetics.com



A world leader in magnetic technology

