



TEGERA® INFINITY 8805



Learn more

SUPER SOFT, PALM DIPPED, CUT B GLOVE

Dexterous cut resistant glove, level B, with touchscreen function. Ultra-light thanks to 18 gg knitted with CRF® cut resistant technology. Palm dipped with super soft nitrile foam that provides excellent grip on dry surfaces. Reinforced thumb crotch for improved longevity. Suitable for precision work. Breathable materials for all day comfort. Protection against contact heat up to 100°C/212°F. Wide range of sizes means a perfectly fitting glove for everyone. Skin friendly with Derma-test and Oeko-Tex certificate.

CHARACTERISTICS

- Durable
- Extra comfortable
- Good fingertip sensitivity
- Flexible
- Good grip

FUNCTIONS

- Withstands contact heat up to 100°C
- Thin
- For touchscreen
- Approved for handling foodstuffs
- Reinforcement between index finger and thumb



PREVENTS RISK OF

Cut injuries, abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt, drying out, chapping

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, dry environments, moist environments, dirty environments

PRIMARY AREAS OF USE

Fine assembly, assembly, machine operating, building and construction, carpentry, painting, installation work, hvac installation, sheet-metal work, engineering, transport work, machine driving, warehouse work, airport work, metalwork, glass industry work, repair work, paper industry work, service work, shop work

PRIMARY INDUSTRIES OF USE

Pulp and paper, glass, bricks, concrete, metal fabrication, machinery and equipment, mro, automotive, transportation, utilities, building and construction, logistics, facilities, service, retail

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves

CATEGORY Cat. II

COLLECTION Infinity

LINING MATERIAL 18 gg, Carbon, CRF⁺ Technology, HPPE, Nylon, Stainless steel fibre yarn

LENGTH 210-270 mm

DEXTERITY 5

GRIP DESIGN Foam grip pattern

COLOUR Grey, Yellow

PAIRS PER: BUNDLE/CARTON 6/120

DISPLAY TYPE Bulk pack

DIPPING Palm-dipped

DIPPING MATERIAL Nitrile foam, Waterbased PU

CUFF STYLE Knitwrist cuff

CUFF MATERIAL Textile

CUT RESISTANCE (EN ISO 13997) Cut resistance level B

CUT RESISTANCE (EN ISO 13997) TDM: 9N

INNER MATERIAL SPECIFICATION Nylon, HPPE (High performance polyethylene), Stainless steel fibre yarn, Carbon thread

OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE



TP TC 019:2011



EN ISO 21420:2020



Contact heat rating valid for palm area only

FEATURES



SIZE		ARTICLE NUMBER	EAN
5	XXS	8805-5	7340118328089
6	XS	8805-6	7340118319322
7	S	8805-7	7340118319339
8	M	8805-8	7340118319346
9	L	8805-9	7340118319353
10	XL	8805-10	7340118319308
11	XXL	8805-11	7340118319315

ejendals

Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com