


KEMET Part Number: SHBC24W-2R4A0174V
(UALS4W2R1A0311)

KEMET, SHBC, AC Line Filters, Normal Mode, 174 uH, 20%



Dimensions

D	57.6mm MAX
L	57.6mm MAX
T	57.6mm MAX
LL	9mm +/-3mm
S	24mm NOM

Packaging Specifications

Packaging:	Tray
Packaging Quantity:	45
Weight:	222 g

General Information

Series:	SHBC
Style:	Through-Hole
Features:	Low Core Loss, High Frequency Drive
RoHS:	Yes
Miscellaneous:	50 (K) Temperature Rise Max.

Specifications

Inductance:	174 uH
Inductance Tolerance:	20%
Current:	20 A
Temperature Range:	-40/+125°C
DC Resistance:	11.8 mOhms