

## Datasheet

# 6 Piece Precision Screwdriver Bit Set

RS Stock number [668-5727](#)



### Material

Chrome molybdenum steel (cr-mo#8660) for Hex/Torx/Slotted/Phillips/Pozidriv,

Chrome vanadium steel (6150) for nut screwdriver bit and extendable blade

High carbon steel for open-end wrench sd bits

Stainless steel for pliers(420)

PS for magnifier and gripping handle

Aluminium handle

### Finish

Chrome plate finish for bits

### Hardness

Heat treated to HRC 54~58 for bits

Heat treated to HRC 38~48 for nut sd bits

### Contents

1pc-Extendable alum bit driver handle

30pc-Precision screwdriver bits 28mm length

Slotted:1.0, 1.5, 2.0, 2.5, 3.0, 3.5, 4.0

Phillips: 000, 00, 0, 1

Pozi: 0, 1



**Contents Continued**

Star: t4, t5, t6, t7, t8, t9, t10, t15, t20

Hexagon: 0.7, 0.9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0

6pc-Precision nut screwdriver bits

Size :2.5 , 3.0, 3.5 ,4.0 ,4.5 ,5.0

5pc-precision open-end wrench screwdriver bits

Size: 4.0, 4.5, 5.0, 5.5, 6.0

1pc- Mini electronic diagonal pliers

1pc- Magnifier

1pc- 4mm flexible shaft

1pc- Plastic griping pick up

1pc- Zip pouch