



Pushing Performance  
Since 1945

# D SUB MA turned contact\_AWG 22-26\_PL1



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 67 000 5576                                                                |
| Specification      | D SUB MA turned contact_AWG 22-26_PL1                                         |
| HARTING eCatalogue | <a href="https://harting.com/09670005576">https://harting.com/09670005576</a> |

## Identification

|                 |               |
|-----------------|---------------|
| Category        | Contacts      |
| Series          | D-Sub         |
| Identification  | Standard      |
| Type of contact | Crimp contact |

## Version

|                       |                   |
|-----------------------|-------------------|
| Termination method    | Crimp termination |
| Gender                | Male              |
| Manufacturing process | Turned contacts   |

## Technical characteristics

|                               |                             |
|-------------------------------|-----------------------------|
| Conductor cross-section       | 0.13 ... 0.33 mm²           |
| Conductor cross-section [AWG] | AWG 26 ... AWG 22           |
| Contact resistance            | ≤10 mΩ                      |
| Stripping length              | 4.5 mm                      |
| Performance level             | 1<br>acc. to CECC 75301-802 |

## Material properties

|                     |                     |
|---------------------|---------------------|
| Material (contacts) | Copper alloy        |
| Surface (contacts)  | Noble metal over Ni |
| RoHS                | compliant           |
| ELV status          | compliant           |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                |
|--------------------------------------|----------------|
| China RoHS                           | e              |
| REACH Annex XVII substances          | Not contained  |
| REACH ANNEX XIV substances           | Not contained  |
| REACH SVHC substances                | Not contained  |
| California Proposition 65 substances | Yes            |
| California Proposition 65 substances | Lead<br>Nickel |

## Commercial data

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Packaging size                 | 100                                        |
| Net weight                     | 0.13 g                                     |
| Country of origin              | Switzerland                                |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140086609                              |
| eCl@ss                         | 27440204 Contact for industrial connectors |
| ETIM                           | EC000796                                   |
| UNSPSC 24.0                    | 39121522                                   |