

PHE F100NRTYRE



Size	F100
Nominal torque (Nm)	675
Nominal torque (lbft)	497.85
Max torque (Nm)	1517
Max torque (lbft)	1118.88
Max speed (r/min)	2600
Weight (kg)	0.95
Weight (lbs)	2.09