

Features

- 2 Gang
- Blank
- White
- Stylish smooth profile plate

RS PRO Plug Sockets

RS Stock No.: 0845489



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Suitable for domestic, commercial and industrial installations.
- Electrophoretically coated plate and back box
- Suitable for use with standard UK 13A plug tops

General Specifications

Dimensions (mm)	140 (W) x 80 (H) x 42 (D)
Plate Fixing Centres (mm)	120.6
Style	Metal Clad
Insert Colour	White
Warranty (Years)	20

Mechanical Specifications

Termination Type	Screw
Terminal Size (mm)	Ø5
Terminal Torque Value (Nm)	2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4
Twin Earth Terminals	Yes
Double Pole Switch	Yes
Supplied Back Box Depth (mm)	40
Back Box Knockouts - Total (mm)	7 x Ø20
Back Box Earth Terminal Supplied	Yes
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Frequency (Hz)	50
Resistive Load Rating (A)	13

Approvals

Standards Met	BS 1363-2
---------------	-----------