

Component connector - BES 6-LA 24 SO - 3048807

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Component connector, Sleeve length: 16.5 mm, Length: 8.7 mm, Width: 12.2 mm, Height: 58.9 mm

The illustration shows product BES 6-1N4007



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 291149
Weight per Piece (excluding packing)	7.74 g
Custom tariff number	85366990
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

General

Insulating material	PA
Inflammability class according to UL 94	V2

Dimensions

Width	12.2 mm
Length	8.7 mm
Height	58.9 mm
	35.9 mm

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199

Component connector - BES 6-LA 24 SO - 3048807

Classifications

eCl@ss

eCl@ss 5.0	27141145
eCl@ss 5.1	27141145
eCl@ss 6.0	27141149
eCl@ss 7.0	27141149

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002018
ETIM 5.0	EC002018

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
