

IN 30 LK 8

Screwdriver bit socket 3/8"

with ball end, for in-hex screws, long pattern

Code **1505750** ETIM **EC002157**

EAN **4010886815632** UNSPSC **27-11-17-01**

Country of origin **Germany** eCI@ss **21-04-04-02**

Customs tariff number
82079030



10 **3/8"**

Article description

- Square drive as per DIN 3120 - C 10, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- Total swivel angle approx. 15-20°

Article information

| | | | |
|--|------------------------------|---------------------------|------------------------------------|
| Contents (Qty of pieces) | 1 | Standard | DIN 3120 - C10 ISO 1174 |
| Net weight [kg] | 0,091 kg | Width across flats 1 [mm] | 8 |
| Total length [mm] | 132 mm | Backup | Ball Catching Cricket |
| Surface | chrome-plated | Tip length | 102,0 mm |
| Material | Chrome-vanadium steel | Insert Ø Actuator | 17,5 mm |
| Drive connector square female (metric) | 10,0 mm | Total swivel angle | 15-20° |
| Drive connector square female [inch] | 3/8" | | |