

Features

- **Secure Isolation** – Effectively locks out wall switches, panel buttons, and rotary switches to prevent unauthorized or accidental operation.
- **Dual Mounting Options** – Can be permanently mounted with screws or temporarily with industrial-grade double-sided adhesive tape.
- **Transparent Cover Design** – Clear top cover allows full visibility of switch positions, labels, and nameplates without removal.
- **Padlock Compatibility** – Equipped with holes to accommodate up to **2 padlocks** for enhanced lockout security.
- **Durable Construction** – Engineered to withstand **dust, light chemical exposure, and impacts**, ideal for industrial environments.
- **Easy Installation** – Simple and quick to install on various surfaces and switch types.

RS PRO Wall Switch Lockout Device - Large

RS Stock No.: 0694377



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *The Wall Switch Lockout Device offers a reliable and highly visible solution for isolating wall-mounted electrical controls during maintenance or servicing.*
- *Designed for easy installation, either via screws or heavy-duty adhesive tape—no special tools required.*
- *Prevents accidental or unauthorized operation of switches, ensuring worker safety and regulatory compliance.*
- *Features a transparent top cover for convenient viewing of switch information without disrupting lockout.*
- *Built for industrial use, it resists environmental wear and supports use of up to 2 padlocks for team-based lockout procedures.*
- *Ideal for use in manufacturing plants, utility panels, commercial buildings, and electrical service areas.*

General Specifications

Type	Wall Switch Lockout
Material	Base: High-strength ABS material. Cover: Clear, impact-resistant Polycarbonate material.
Colour	Red with clear cover
Padlock holes	02
Package	PE-LD

Mechanical Specifications

Outer Length	158mm
Inner Length	134mm
Outer Width	98mm
Inner Width	74mm
Outer Height (Including shackle point)	136mm
Accept padlock shackle up to	7.8mm
Hole dia. For mounting screws	4mm
Weight	166 Grams

Operation Environment Specifications

Withstand temperature	Base (ABS): -20°C to +80°C / -4°F to +176°F Cover (Polycarbonate): -40°C to +120°C / -40°F to +248°F
------------------------------	---

