

# 18V Linetrimmer BL LXT

## DUR189Z

Model DUR189 is the successor to DUR184L. ADT adjusts speed and torque during operation for optimum performance.



### TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	18 v
Noise sound pressure	78 dB(A)
Noise K factor	2.0 dB(A)
Spindle Size	M8 x 1.25 RH
Cutting diameter	300 mm
Maximum Output	240 w
No Load Speed	4000 / 5000 / 6000 rpm
Vibration K factor	0.4 m/sec <sup>2</sup>
Vibration	2.5 m/sec <sup>2</sup>
Net weight	3.0 - 3.3 kg

### USER BENEFITS

- Brushless motor
- Automatic Torque Drive Technology: RPM is automatically shifted between 4,000 - 6,000 min<sup>-1</sup> according to density of weeds. This allows for better energy saving and lower noise levels.
- Length adjustable bending pipe shaft
- Overload protection
- Electric brake
- Soft start
- Constant speed control
- Reverse switch for grass clipping removal
- Wire guard reduces risk of damaging fences, flowers or ornaments: Foldable for convenience
- Speed indicator on control panel shows 3x RPM levels, plus status of overload, overheat and over-discharge.
- Small protector for better view of cutting area

[Link to product - makitauk.com](https://www.makita.com)



# RELATED PRODUCTS

(Recom

## ■ OTHER