

ME MAX 6,2 DKL WH TRANS - Housing cover



2200564

<https://www.phoenixcontact.com/gb/products/2200564>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Cover, width: 6.3 mm, height: 40.2 mm, depth: 3.6 mm



Your advantages

- Easy, tool-free mounting

Commercial data

Item number	2200564
Packing unit	100 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Sales key	ACHABZ
Product key	ACHABZ
GTIN	4046356610773
Weight per piece (including packing)	0.575 g
Weight per piece (excluding packing)	0.484 g
Customs tariff number	85389099
Country of origin	DE

ME MAX 6,2 DKL WH TRANS - Housing cover



2200564

<https://www.phoenixcontact.com/gb/products/2200564>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX 6,2..
Type	Cover
Ventilation openings present	no

Dimensions

Width	6.3 mm
Height	40.2 mm
Depth	3.6 mm

Material specifications

Color	transparent/white
Flammability rating according to UL 94	V2
CTI according to IEC 60112	275
Insulating material	IIIa
Housing material	PC
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

PCB data

Type of PCB mount	Latching
-------------------	----------

ME MAX 6,2 DKL WH TRANS - Housing cover



2200564

<https://www.phoenixcontact.com/gb/products/2200564>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2200564>



UL Recognized

Approval ID: E240868

ME MAX 6,2 DKL WH TRANS - Housing cover



2200564

<https://www.phoenixcontact.com/gb/products/2200564>

Classifications

ECLASS

ECLASS-13.0	27190603
-------------	----------

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME MAX 6,2 DKL WH TRANS - Housing cover



2200564

<https://www.phoenixcontact.com/gb/products/2200564>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk