



**Part Number :** [191930360](#)

**Product Description :** VersaKrimp Ring Tongue Terminal for 3/0 AWG Wire, Closed-Brazed Barrel, Stud Size 5/16" (M8), Carton

**Series Number :** 19193

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Number :** K-390-56



---

## Documents & Resources

### Drawings

[191930360 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |  |
|--------------------|--|
| GADSL/IMDS         | Compliant with Exemption 44  |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant   |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21   |
| REACH SVHC         | Not Contained per D(2025)4165-DC<br>(25 June 2025)   |
| EU RoHS            | Compliant per EU 2015/863  |

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|              |  |
|--------------|--|
| Status       | Active   |
| Category     | Ring and Spade Terminals   |
| Series       | 19193  |
| Description  | VersaKrimp Ring Tongue Terminal for 3/0 AWG Wire, Closed-Brazed Barrel, Stud Size 5/16" (M8), Carton |
| Keyword      | Ring Terminal, Ring Terminals  |
| Product Name | VersaKrimp   |
| Style        | Ring   |
| Type         | Ring Terminal, Metric Ring Terminal  |
| UPC          | 800755052510   |

### Agency

|     |         |
|-----|---------|
| CSA | LR18689 |
| UL  | E32244  |

### Physical

|                           |                 |
|---------------------------|-----------------|
| Barrel Type               | Closed - Brazed |
| Insulation                | None            |
| Material - Plating Mating | Tin             |
| Net Weight                | 35.046/g        |
| Packaging Type            | Carton          |
| Stud Size                 | 5/16" (M8)      |

|                             |                      |
|-----------------------------|----------------------|
| Termination Interface Style | Crimp or Compression |
| Wire Insulation Diameter    | 19.02mm max.         |
| Wire Size (AWG)             | 3/0                  |
| Wire Size mm <sup>2</sup>   | 95.00                |

---

## Application Tooling

### Global

| Description                                    | Part Number      |
|--|------------------|
| Die Set (Large) for the HHLS Hydraulic Crimper | <u>192900028</u> |