

**MECHANICAL PROTECTION****GUIDE 650**

PRECISION | SEAMLESS

Ultra-thin and airy nylon work glove that feels like a second skin. Extreme fingertip sensitivity. PU palm dipped. For precision work

- ▶ 18GG Ultra-thin
- ▶ Polyurethane (PU)
- ▶ Latex free
- ▶ Extreme fingertip sensitivity
- ▶ Sizes 5-11



CE CATEGORY 2



EN 420:2003

EN 388:2016
3121X**SUITABLE FOR:**

Building, Construction & Road | Automotive & transportation | Logistics & retail | Machinery & equipments | Utilities & services

PROTECTION AGAINST:

Abrasions | Scratchers | Blisters

ERGONOMIC FEATURES:

Tight fit | Ventilating | Ultra thin | Rolled knitted cuff | Good dry grip | Good wet grip

QUALITY FEATURES:

Natural latex free | REACH compliant

COLORS:

Blue | Black

OUTSIDE RAW MATERIAL:

Polyurethane (PU) | Palm dipped | Smooth finish

INNERSIDE RAW MATERIAL:

Elasthane | Nylon

GLOVE THICKNESS:

0.77 mm

GAUGE:

18

MECHANICAL PROTECTION

GUIDE 650

PRECISION | SEAMLESS

ART.NO	DESCRIPTION	BUNDLE	CARTON	UNIT	AVAILABLE IN PAIR/PCS
223536565	GLOVE GUIDE 650 5	12	120	Pair	No
223536566	GLOVE GUIDE 650 6	12	120	Pair	No
223536574	GLOVE GUIDE 650 7	12	120	Pair	No
223536582	GLOVE GUIDE 650 8	12	120	Pair	No
223536590	GLOVE GUIDE 650 9	12	120	Pair	No
223536608	GLOVE GUIDE 650 10	12	120	Pair	No
223536616	GLOVE GUIDE 650 11	12	120	Pair	No