

Robust, long-cuffed PVC gloves, offering grip, comfort and chemical resistance

- **Heightened protection:** With their special PVC and nitrile formulation, AlphaTec® 04-005 protective gloves blend high-level chemical resistance*, abrasion protection and sustained flexibility, even at low temperatures
- **Food handling compliance:** These latex-free industrial gloves also satisfy FDA and EU food processing and hygiene norms, resulting in ideal food safety gloves for a variety of applications
- **Increased comfort:** Thanks to their 13-gauge seamless cotton design, they offer an excellent balance between personal protection and user comfort
- **Enhanced features:** These AlphaTec® gloves' foam grip design guards against oil and grease, while maintaining superb grip in wet and oily environments, and their 38cm/15" glove length further enhances wearer protection
- **Advanced ergonomics:** In addition, their ergonomic hand shape further enhances wearer comfort and makes them easy to use over a prolonged period



*6 chemicals certified (JKLMPT) out of 18 EN ISO 374:2016; an additional 5 chemicals (AFNOS) have achieved a permeation level 2 or higher in an accredited lab

Industries

- Food Processing
- Infrastructure Maintenance
- Maintenance
- Chemical

Applications

- All food processing applications that have food contact
- Chemical Handling
- Maintenance
- Cleaning

Key Features

- **Robust PVC and nitrile compound:** Protection from varied chemical hazards*
- **EU and FDA compliance:** Suitable food safety gloves for multiple applications
- **13-gauge seamless cotton design:** A balance of hand protection and comfort

*6 chemicals certified (JKLMPT) out of 18 EN ISO 374:2016; an additional 5 chemicals (AFNOS) have achieved a permeation level 2 or higher in an accredited lab



Performance Standards

CE 0493



Specifications

BRAND STYLE	DESCRIPTION	GAUGE	SIZE	LENGT H	COLOR	PACKAGE
AlphaTec® 04-005	Liner Material: Cotton Coating Material: PVC + Nitrile	13	8, 9, 10, 11	380 / 15	Blue	12 pairs in a bag ,60 pairs in a carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.