

ACTIVARMR™

47-401

Ideal alternative to PVC and light leather gloves

Previously known as: Nitratough™ N230Y



Oil



Medium Duty

Abrasion-resistant gloves offering an ideal alternative to PVC and light leather gloves

- **Enhanced protection:** ActivArmr® 47-401 nitrile gloves are composed of a 100% cotton interlock liner, which ensures superb abrasion resistance as well as excellent dexterity and flexibility
- **Specialized features:** These ¾ dipped abrasion-resistant gloves afford excellent oil repellence
- **Elevated comfort:** In addition, ActivArmr® 47-401 safety gloves feature an elasticated knitwrist, delivering a snug and comfortable fit



Industries

- Metal fabrication
- Maintenance

Applications

- Assembly and finishing
- Maintenance
- Metal Fabrication

ACTIVARMR™

47-401

Ideal alternative to PVC and light leather gloves

Previously known as: Nitratough™ N230Y

Key Features

- **100% cotton interlock liner:** Superior abrasion resistance
- **☒ dipped nitrile coating:** Outstanding oil-repellent gloves
- **Elasticated knitwrist:** A snug fit assured

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 47-401	Finishing: ¾ Coated Coating Material: Nitrile Liner Material: Cotton Jersey Cuff Style: Knitwrist	6, 7, 8, 9, 10, 11	235-282 mm	Yellow	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

